

FEATURES

- **Non-Releaseable Design:** Ensures a secure and permanent fastening solution.
- **Nylon Material:** Offers durability and resistance to wear and tear.
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight.
- **Tensile Strength of 34 kg:** Provides strong holding capability for heavy-duty applications.
- **Length of 300 mm:** Accommodates a maximum bundle diameter of 74 mm, ideal for larger cable bundles.
- **Width of 4.8 mm:** Balances flexibility with strength for versatile use.
- **Maximum Operating Temperature of 85°C:** Suitable for environments with elevated temperatures.

RS PRO 300mm Nylon Cable Tie, Non-Releaseable

RS Stock No: 656-053



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a robust and reliable cable tie solution designed for secure bundling and organising of cables and wires. This non-releasable cable tie is ideal for applications requiring a strong and durable fastening solution, providing excellent tensile strength and UV resistance for both indoor and outdoor use.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	74 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---