

PREVOST FILTRATION - SINGLE UNITS

Splitter - 2 outputs



Part number	Female thread	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)
ATU D100	G1/8	5.00 / 50.00	12.00	0,212
ATU D101	G1/4	5.00 / 50.00	12.00	0,212
ATU D103	G1/2	5.00 / 50.00	12.00	0,5

