

## WHL-L7

### Tool trolley workster

with 7 drawers

Code	ETIM
3033708	EC011808
EAN	UNSPSC
4010886950364	56-12-18-02
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
94032080	



### Article description

- Body:
  - Dimensions: H 1045 x W 785 x D 510 mm
  - Work platform with PP plastic cover with front flattening and roll protection edge, as well as small additional storage compartments, can and screwdriver holder
  - Stainless steel insert in top
  - With handle for easy pushing, pulling and turning
  - Side walls with Euro perforation 10 x 38 mm to fix hooks and tools
  - Sheet steel, corrosion resistant and scratch-proof powder-coated, GEDORE blue
  - Sides rounded off – minimising abutting edges
  - Body welded, self-supporting and torsionally rigid
- Drawers:
  - Single pull-out stop prevents more than one drawer from being opened, one-hand operation
  - Central locking with a cylinder lock and safety key, bends under stress without breaking
  - 5 flat, wide drawers (W 640 x D 400) with full extension
  - 2 high, wide drawers (W 640 x D 400) with full extension
  - Guide rails with ball bearings
  - Load-bearing capacity per drawer 40 kg
  - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Chassis:
  - Total load capacity 500 kg
  - 4 smooth running wheels on ball bearings (swivel castors Ø 125 mm) with thread guard, two with total brake
  - Also in case of maximum loads: smooth running, manoeuvrability and track-keeping
- Options:
  - Can be individually subdivided with lengthwise and crosswise dividers
  - Special colours and designs on request
  - Delivery without tools and accessories

### Article information

Contents (Qty of pieces)	1	Load capacity per drawer [kg]	40 kg
Net weight [kg]	84 kg	Drawer type	5x Type 1, H = 80 mm 2x Type 2, H = 160 mm
Total length [mm]	785 mm	Fixed roller diameter (2x)	125
Total width [mm]	510 mm	Swivel castor diameter with brakes (2x)	125
Total height [mm]	1.045 mm	Single pull-out stop	yes
Surface	powder-coated	Number of wheels	4
Material	sheet steel	Working height	1.045
Colour	GEDORE blue, RAL 5017	Static load carrying capacity [kg]	500 kg
Dimension (L x W x H)	1.045 mm x 510 mm x	RAL colour tone	blue
Number of drawers	7		