


Technical data sheet

Article number:
151-00437

HDM25



Product Group	Harness clip for heavy duty applications, for screws or threaded bolts
Product Family	Standard Torque Mounts
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
CE Certification	No
Fixation Method	Screw Mounting and Rivet
Flammability	UL 94 HB
for Hole Ø (FH)	6.2 mm
Height (H)	16.7 mm
Length (L)	36.3 mm
Mounting Screw Type	#1/4" (M6) Screw
Operating Temperature	-40 °C to +105 °C
Package Content	100 pcs.
Package Content packed in	pack
ROHS compliant	Yes
Stud Ø	6.2 mm
UV-Stabilised	Yes
Width (W)	19.3 mm

