

Supply Voltage (20.4 to 26.4)	26	V
Link Cable Wire Gauge	18	AWG
Link Wire Resistance	0.02095	ohms/m

Tap	Cable Length (m)	Safety Device	User Defined Device Current (mA)	Tap + Device Current (mA)	Total Current (mA)	Voltage level @ Tap
1	10	SensaGuard_New		67	1192	25.43
2	10	SensaGuard_New		67	1125	24.90
3	10	SensaGuard_New		67	1058	24.40
4	10	SensaGuard_New		67	991	23.93
5	10	SensaGuard_New		67	924	23.49
6	10	UserDefined_EMSS		40	857	23.08
7	10	UserDefined_EMSS		40	817	22.69
8	10	UserDefined_EMSS		40	777	22.32
9	10	SensaGuard_New		67	737	21.97
10	10	SensaGuard_New		67	670	21.65
11	10	SensaGuard_New		67	603	21.37
12	10	SensaGuard_New		67	536	21.11
13	10	SensaGuard_New		67	469	20.89
14	10	SensaGuard_New		67	402	20.70
15	10	SensaGuard_New		67	335	20.54
16	10	SensaGuard_New		67	268	20.41
17	0	SensaGuard_New		67	201	20.40
18	0	SensaGuard_New		67	134	20.39
19	0	SensaGuard_New		67	67	20.39
20	0			0	0	NA
21	0			0	0	NA
22	0			0	0	NA
23	0			0	0	NA
24	0			0	0	NA
25	0			0	0	NA
26	0			0	0	NA
27	0			0	0	NA
28	0			0	0	NA
29	0			0	0	NA
30	0			0	0	NA
31	0			0	0	NA
32	0			0	0	NA