

Han-Eco 10B-HTE-for DL-M20-glanded



Part number	19 43 110 0425
Specification	Han-Eco 10B-HTE-for DL-M20-glanded
HARTING eCatalogue	https://b2b.harting.com/19431100425

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Hoods
Description of hood/housing	With integrated cable gland

Version

Locking type	Double locking lever
Size	10 B
Version	Top entry
Cable entry	1x M20

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP66
Clamping range	6 ... 13 mm

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3
----------------	--

Commercial data

Packaging size	1
----------------	---



Pushing Performance

Commercial data

Net weight	119 g
Country of origin	Germany
European customs tariff number	85389099
