



Sliver for SFF-TA-1002

TE Internal #: 2292069-1

TE Sliver, Cable Plug Assembly, Right Angle, Cable-to-Board, 74
Position, Surface Mount, Sliver for SFF-TA-1002, Internal I/O
Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Internal I/O Connectors



Internal I/O Connector Type: **TE Sliver**
Connector Mates With: **Cable Plug Assembly**
PCB Mount Orientation: **Right Angle**
Connector System: **Cable-to-Board**
Number of Positions: **74**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Internal I/O Connector Type	TE Sliver
Connector Mates With	Cable Plug Assembly
Connector System	Cable-to-Board

Configuration Features

Number of Rows	2
PCB Mount Orientation	Right Angle
Number of Positions	74

Contact Features

PCB Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	.9 A



Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
--	-----------------

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	.6 mm[.023 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 2821745-2 SLIVER C/A, 74P, R/A TO R/A, 25GHZ, 85OHM	 TE Part # 2821757-2 SLIVER C/A, 74P, R/A TO R/A,25GHZ, 100OHM	 TE Part # 2821753-1 SLIVER C/A, 74P, STR TO STR,10GHZ, 100OHM	 TE Part # 2821746-2 SLIVER C/A, 74P, STR TO R/A, 25GHZ, 85OHM
 TE Part # 2317823-1 CABLE PLUG KIT, SLIVER 74P	 TE Part # 2821754-2 SLIVER C/A, 74P, R/A TO R/A,10GHZ, 100OHM	 TE Part # 2821753-2 SLIVER C/A, 74P, STR TO STR,10GHZ, 100OHM	 TE Part # 2821755-2 SLIVER C/A, 74P, STR TO R/A,10GHZ, 100OHM
 TE Part # 2820396-2 SLIVER C/A, 74P, STR TO STR, 10GHZ, 85OHM	 TE Part # 2821746-1 SLIVER C/A, 74P, STR TO R/A, 25GHZ, 85OHM	 TE Part # 2820396-1 SLIVER C/A, 74P, STR TO STR, 10GHZ, 85OHM	 TE Part # 2821758-1 SLIVER C/A, 74P, STR TO R/A,25GHZ, 100OHM
 TE Part # 2821755-1 SLIVER C/A, 74P, STR TO R/A,10GHZ, 100OHM	 TE Part # 2821756-1 SLIVER C/A, 74P, STR TO STR,25GHZ, 100OHM	 TE Part # 2821376-2 SLIVER C/A, 74P, STR TO STR, 25GHZ, 85OHM	 TE Part # 2821757-1 SLIVER C/A, 74P, R/A TO R/A,25GHZ, 100OHM
 TE Part # 2821376-1 SLIVER C/A, 74P, STR TO STR, 25GHZ, 85OHM	 TE Part # 2821756-2 SLIVER C/A, 74P, STR TO STR,25GHZ, 100OHM	 TE Part # 2821385-1 SLIVER C/A, 74P, R/A TO R/A, 10GHZ, 85OHM	 TE Part # 2821385-2 SLIVER C/A, 74P, R/A TO R/A, 10GHZ, 85OHM


Also in the Series | [Sliver for SFF-TA-1002](#)



Connector Hardware(1)




Internal I/O Cable Assemblies(105)




Internal I/O Connectors(133)

Customers Also Bought



TE Part #5788797-1
09 HTMSFL ASSY RA 318 (SL,BL)



TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R



TE Part #2102772-1
DC, 7Row, Half Left End, MULTIGIG RT 2R



TE Part #1-2176331-3
CRGP 2512 100R 1%




TE Part #6-2176307-7
RP 1E 0.1W 60K4 0.1% 25PPM 5K RL



TE Part #6-1879215-8
CPF 0402 23K2 0.1% 25PPM 1K RL




TE Part #1571983-3
GDH02STR04=DIP SWITCH



TE Part #3-641208-4
04P MTA156 HDR ASSY FL ST 30AU



TE Part #6450863-5
MBXLE VERT RCPT 7ACP



TE Part #2828573-1
MEZALOK , SOCKET, COVER, 12MM

Documents

Product Drawings

RCPT ASSEMBLY SMT RA 74 POSN MBC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2292069-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2292069-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2292069-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Sliver Internal Cabled Interconnect Solutions Brochure \(Chinese\)](#)

Agency Approvals

[UL Report](#)

English