

Eaton 248442

Catalog Number: 248442

Eaton Distribution parts. Shunt release, up to 125A, 110-415V, 1.5HP

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248442
EAN	Product Length/Depth
4015082484422	80 mm
Product Height	Product Width
75 mm	39.1 mm
Product Weight	Compliances
0.158 kg	RoHS conform
Certifications	
EN45545-2	
IEC 61373	

Product specifications

Used with

Shunt releases

Type

Accessory

Accessory for miniature
circuit breaker

Application

Switchgear for industrial and advanced commercial applications

Accessory/spare part type

Shunt release

Mounting method

For fitting on left to: AZ

Additional equipment required

Shunt release (for power circuit breaker)

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-5 °C

Assembly width

1.5 TE

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Number of poles at main contact unit - max

1

Number of switches (fault signal)

0

Voltage type

AC

Functions

Shunt release (for power circuit breaker)

Device fitting

Resources

Declarations of conformity

[DA-DC-03_Z-LHASA](#)

Drawings

[eaton-dimensions-mas-lhasa.eps](#)

[eaton-dimensions-ma-lhasa.jpg](#)

eCAD model

[ETN.Z-LHASA_230.edz](#)

Installation instructions

[IL019166ZU](#)

mCAD model

[z_lhasa_230.stp](#)

[z_lhasa_230.dwg](#)

Wiring diagrams

[Z7_asa](#)

Miniature circuit breaker (MCB)

Rated operational voltage (Ue) - max

230 V

Rated switch current

2 A

Suitable for current of main contact unit - max

2 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia