

DAY-LITE LED

The slim profile Day-Led general luminaire can be used indoor or out.

- Extended life, high performance LED light source
- Energy saving LED control technology
- Slim, clean style
- Available in non-maintained or maintained operation
- Rated to IP65, with screw fixed security



Specification	Self-contained luminaire
	Electrical & operational
Input voltage	220-240v 50Hz
Duration	3 hours (maintained and non-maintained)
Battery	High temperature nickel metal hydride
Charger	Constant current
Charging monitor	Green LED
Recharge period	24 hours
Lamp	LED strip light
Lamp rating:	1w
Consumption:	NM- 12mA, M-27mA
	Construction & Installation
Cable entry	Moulded locations, 20mm
Construction	Polycarbonate body in white. Clear optically engineered diffuser, screw fixed to base
Environment	0 – 25°C ambient
Ingress class	IP65
Dimensions lwd (mm)	343 x 98 x73
Weight (kg)	1.1
Product standards	Designed & manufactured to meet the BSEN60598.2.22 regulations
To order	
Product code	Description
XW2LS11	Day-LED, NM 3 hour duration, white trim
XW3LS11	Day-LED, M 3 hour duration, white trim
Accessories & Legends	
XTR	Semi-recess bezel in white
Self-adhesive legends	
Code	Description
RSEN23560X	Self-adhesive sticker set

Mount height m	Escape route (min, 1 lux)				Open area (min, 0.5 lux)			
2.5		4.3	2.4		4.2	8.5	4.2	1.3
3.0		4.9	1.0		4.9	10.0	4.1	
4.0						6.7	2.1	

Spacing data for NM3