



Datasheet

ENGLISH

RS Pro LED Bench Magnifier, 12 dioptre, 3 dioptre, Integral Base, 2W

Stock No: 808-7046



Technical Specifications

Description:	Compact LED table magnifier lamp
Voltages Available:	220v & 240v, 50Hz
Magnifier:	100mm(4") diameter lens
Magnification:	1.75x (3 dipotre) & inbuilt 4x (12 dioptre)
Sun Protector Cap:	YES
Light Type:	30 x White LED mini bulbs = 2w; 6500 Kelvin; Energy efficient;
Cable Length:	1.5m
Table Clamp/Base	Integral Base

HOW TO USE

1. Insert the 220v or 240v plug into a conveniently located electrical socket
2. Switch the lamp on by using the on/off switch located on top on the base. The lamp is now ready to use.
3. Adjust your lamp head position to suit your need.

IMPORTANT! - SAFETY INSTRUCTIONS

WARNING: When using electrical products, important safety precautions must be adhered to in order to reduce the risk of fire, electric shock and personal injury.

PLEASE READ THE FOLLOWING CAREFULLY:

1. Indoor use only:
 - a. Room temperature from -20 to +40 degrees centigrade
 - b. Humidity: Less than or equal to 95%
2. Do not expose the lamp to:
 - a. High temperatures
 - b. Water, steam or damp conditions
 - c. Corrosive, flammable liquids, or gaseous / explosive atmospheres
3. Do not abuse the cord. Never carry the lamp by the cord or pull the cord to disconnect the lamp. Keep the cord away from heat, oil or sharp objects
4. Disconnect your lamp when not in use.
5. Never attempt to disassemble or repair the lamp, unless you are a qualified electrician
6. **CAUTION:** Never leave the magnifier lens unattended in direct sunlight or where light can shine through it - This constitutes and fire hazard!

CE Declaration of Conformity We declare that this product
complies with the Electromagnetic Compatibility Directive and the
Low Voltage Directive

RS COMPONENTS UK
PO BOX 99
CORBY
NORTHANTS, NN17 9RS
United Kingdom

Tel: +44 (0)8457 201201
WEB: rswww.com

Fax: +44 (0)845 8509911
RoHS Compliant

