



ENGLISH

# Datasheet

## RS Pro 10 mm Air Drill

RS Stock No: 137-0886



RS Pro Air Drill, 10 mm keyless chuck air drill with a magnesium body. Lightweight feel and a high performance motor maximise output speed. Ergonomic grip design for better manoeuvrability, while the durable motor designed with high balance for precision work without vibration. Speed control trigger for precision work and a thumb lever to switch drive direction with one finger.

### Features and Benefits

- Magnesium body
- Rear exhaust through handle
- 3/8" / 10 mm keyless chuck
- Side-mounted forward/reverse shift
- Triple planetary gear system
- Keyless chuck
- Powerful air motor
- Positive trigger action

### SPECIFICATIONS

Material	Magnesium
Chuck Size	3/8 in / 10 mm
Vibration	0.9 m/s <sup>2</sup>
Sound	92.5 dBa
Free Speed	1,800 rpm
Weight	2.6 lb / 1.16 kg
Length	203 mm
Air Inlet Thread Size	1/4 in
Minimum Hose Size	3/8 in / 10 mm
Average Air Consumption	4.28 cfm / 121.4 l/min