



**Part Number :** [734150972](#)

**Product Description :** MMCX Plug, Straight, Crimp, RG-178/RG-196, Brass Body, Gold (Au) Plating, One Piece Per Bag, 50 Ohms

**Series Number :** 73414

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources

### Drawings

[734150972\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[735970590-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Plug, Straight, Crimp, RG-178/RG-196, Brass Body, Gold (Au) Plating, One Piece Per Bag, 50 Ohms
Product Name	MMCX
Style	Cable
Type	Microminiature
UPC	800756723358

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	0.460/g
Orientation	Straight
Packaging Type	Individual Bag

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-178, RG-196

---

This document was generated on Aug 05, 2025