

Technical data sheet

Article number:
450-20041

RMS 139-38

Product Group	Heat shrinkable cable repair sleeves
Product Family	RMS
Material	Polyolefin, chemically cross-linked (PO-X)
Colour	Black (BK)
Adhesive	Hot melt adhesive
Dielectric Strength	30 kV/mm
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature - °C	+110 °C
Operating Temperature	-40 °C to +120 °C
Package Content	1000.0 mm
Recov. Ø d max.	38.0 mm
Shrink Ratio	up to 4.5:1
Supplied Ø D min.	139.0 mm
Tensile Strength	17.5 MPa
UV-Stabilised	Yes
Wall (WT)	2.77 mm

HF ✓

RoHS ✓