



LIGHT DRIVES

NEW PRODUCT

I-BUCK™ LED DRIVER MODULES



- ONE TO SIX SERIES WHITE LEDs AT 345mA
- 7.0V TO 30.0V DC INPUT # I-BUCK3.5DC
- 5.0V TO 20.0V AC INPUT # I-BUCK3.5AC
- WATERPROOF
- REVERSE CONNECTION PROOF
- SHORT CIRCUIT PROOF
- EFFICIENCY BETWEEN 76 & 91%
DEPENDING ON DRIVE CONDITIONS
- DIMENSIONS: 16mm X 16mm X 9 mm
- WEIGHT (including wires): 3.3g

I-BUCK 3.5 DC
I-BUCK 3.5 AC

Connections:

Red : +V input
Black: -V input
Orange: +V output (LED +ve)
Green: -V output (LED -ve)

THE I-BUCK 3.5 LED DRIVER MODULE HAS BEEN DEVELOPED AS A HIGHLY COST EFFECTIVE AND MINIATURISED SOLUTION FOR DRIVING LEDs IN A WIDE RANGE OF APPLICATIONS.

THE MODULE IS AVAILABLE IN 2 VERSIONS, ONE FOR DC ONLY INPUT AND ONE FOR AC INPUT.

NO EXTERNAL COMPONENTS ARE REQUIRED.

