

Features

- M25 Thread
- Made from Polyamide 6.6
- Ring Seal, TPERS
- Screw Mount
- IP66
- 10 Pieces per pack

RS PRO Cable Glands

RS Stock No.: 185-6102



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *RS PRO Cable Glands - Excellent solution for cable entries used within Industrial, Automotive, Switchgear and cabinets applications.*

Available in a variety of sizes, these robust cable glands feature a split design allowing for easy installation with an IP66 rating offering excellent protection against moisture and dust. For enhanced protection, the cable glands also feature a halogen-free design preventing harsh chemicals from being released in the event of a fire.

General Specifications

Thread Size	M25 - Metric
Material	Nylon 66
Colour	Black
Fire Behaviour	Halogen free, self-extinguishing
Locknut Included	No
Pack size	10
Sealing	TPE
Thread Pitch	1.5 mm
Thread Length (L)	15 mm
Length	40 mm
Width	40 mm
Height	38.7 mm
Installation Height	23.7 mm
Diameter Screw Head	40 mm

Mechanical Specifications

Material	Polyamide 6.6
Flammability Class UL 94	V-0
Mounting	Screws

Operation Environment Specifications

Minimum Operating Temperature	-40°C
Maximum Operating Temperature	120°C
Operating Temperature Range	-40 to +120°C

IP Rating	IP66
-----------	------

Classification

eCl@ss Version	
UNSPSC Version	