

Electronic housing - ME-IO 18,8 DEV-KIT KMGY - 2202527

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DEV-KIT ME-IO: contains 1 x ME-IO 18,8 housing and pluggable connection technology (HSCH with HSCP), supplied in individual parts

Why buy this product

- Narrow housing with overall width of 18.8 mm
- Plug-in front connection technology
- Optional hole matrix PCB for soldering THT components by hand
- Connection of individual housing modules by means of the optional ME TBUS via DIN rail

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141770
Weight per Piece (excluding packing)	89.0 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color	light gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	113.3 mm
Constructional height	77 mm
Width	18.8 mm

Technical data

Flammability rating according to UL 94	V0
--	----

Electronic housing - ME-IO 18,8 DEV-KIT KMGY - 2202527

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501