

VALUE Cable USB 2.0, C-C, M/M, 60W, white, 1 m

Product No. 11.99.8340
Manufacturer VALUE
Manufacturer No. 11.99.8340
EAN (single piece) 7630049632813



High-quality USB charging cable for smartphones and tablets with improved shielding and the reversible USB-C plug at both ends. Cable sheath made of white textile braiding to match the design of the Apple iPhone 15 products.

- High quality USB 2.0 cable with improved shielding
- With the reversible Type C connectors at both ends
- Gold-plated contacts for low wear at high plugging cycles
- Suitable for data transfer rates of up to 480 Mbit/s
- Supports USB Power Delivery to 20V / 3A

Technical specifications	
Manufacturer	VALUE
Product group	Cable
Product type	USB 2.0 Cable
Colour	white
Length	1 m
Transfer quality	USB 2.0 Hi-Speed 480 Mbit/s
Connection ports	USB Type C (USB-C) Male / USB Type C (USB-C) Male
Side 1 Connector Type	USB Type C (USB-C)
Side 1 Connector Gender	Male

Side 2 Connector Type	USB Type C (USB-C)
Side 2 Connector Gender	Male
Colour (Cable)	White
Maximum data transfer rate	480 Mbit/s
Area of application	External
Power (max.)	60 W
Cable shielding	Screened
Operating temperature min.	0 °C
Operating temperature max.	45 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C
Weight	17 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	60 mm
Depth of packaging (single piece)	90 mm
Package weight (single piece)	0.022 kg