



### Main

Range of product	Mita
Product name	Cableline 50
Product or component type	Installation trunking
Colour tint	White/Grey
Quantity per set	Set of 2

### Complementary

Compartment partitioning	3 compartments
Trunking dimension	180W x 52 mm
Trunking material	Plastic
Front opening size	87 mm
Device composition	White trunking base grey lid (x 3)
Fixing mode	Screw-fixed
Material	UPVC (unplasticized polyvinyl chloride)
Product compatibility	X 25 mm mounting boxes x 35 mm mounting boxes
Length	3000 Mm
Height	180 Mm
Width	52 Mm

### Environment

Standards	ANSI/TIA/EIA-568-B BS 4678-4 BS 6701 BS 7671 BS EN 50174-2 ISO/IEC 11801 EN 50173
Ambient air temperature for operation	-5...60 °C

### Packing Units

Package 1 Weight	2.13 Kg
------------------	---------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**