

Features

- **Impact-Modified Nylon Body** – Built with durable, high-strength material for long-lasting reliability.
- **4.5-Meter Vinyl-Coated Steel Cable** – Provides exceptional flexibility, reach, and resistance to wear.
- **Multi-Application Use** – Suitable for complex lockouts including large panels, gate valves, and oversized equipment.
- **Tool-Free Operation** – Cable can be easily looped, tightened, and secured without special tools.
- **Supports Up to 6 Padlocks** – Allows multiple personnel to secure the same lockout point for enhanced group safety.
- **Performs in Extreme Conditions** – Engineered for reliable performance in harsh industrial environments.

RS PRO Adjustable Cable Lockout With 4.5 Mtrs. 4mm PVC Coated Steel Cable

RS Stock No.: 0710519



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Constructed with a robust impact-modified nylon housing for superior durability.*
- *Equipped with a 4.5-meter flexible steel cable, coated in vinyl to resist abrasion and corrosion.*
- *Ideal for securing complex machinery setups like multiple circuit breaker panels or large gate valves.*
- *Cable can be threaded easily and locked with minimal effort, ensuring quick deployment.*
- *Accepts up to 6 safety padlocks, enabling secure multi-worker lockout procedures.*
- *Designed to withstand extreme environmental conditions, ensuring dependable operation in all settings.*

General Specifications

Type	Multipurpose Cable Lockout
Material	Nylon body, steel cable with vinyl coating
Colour	Red & black
Padlock holes	06
Package	PE-LD

Mechanical Specifications

Cable Thickness	4mm
Cable Length	4.5 meter
Weight	246 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 80°C (-4°F to 176°F)
-----------------------	-------------------------------