

Datasheet

RS Pro Access Control Door Strike, Fail Safe, Fail Secure, 12 V, 24 V, 33 mm

RS Stock No: **741-8240**



Product Details

RS Pro access control door strike of 33 mm, comes with fail safe and fail secure mode. It operates at a voltage rating of 12 V, 24 V. It is tested to 1 million cycles and has lock surface ambient temperature of + 20%.

Features and Benefits

- ANSI release 12 V dc long and short faceplate
- Auto-relocking time delay: 0, 3, 6 or 9 s
- 2000 lbs jaw strength pull testing
- Tested to 1 million cycles
- Lock surface temperature (when power is on) ambient + 20%
- Fail safe/fail secure selectable
- Current draw: 0.25 A at 12 V dc
- Operating temperature range: -10 to +45°C



Specifications:

Failure Mode	Fail Safe, Fail Secure
AC or DC Operation	DC
Supply Voltage	12, 24 V
Width	40 mm
Depth	33 mm
Height	202 mm