

Product data sheet

Specifications



Spacial SF enclosure with mounting plate - assembled - 2000x1000x500 mm

NSYSF2010502DP

Main

Range	Spacial
Extended range	Spacial SF
Application	Multi-purpose
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	500 mm
Enclosure mounting	Floor-standing
Device composition	2 sliding rails 4 mounting plate bracket 1 structure 1 rear panel 1 roof 1 mounting plate 2 door 1 locking system with handle 1 blocking system: left door

Complementary

Structure type	Perforated structure with a pitch of 25 mm Panels and doors built into the structure Formed from a single section Vertical uprights joined with top and bottom frames
Door type	Plain front
Number of doors	Front face: 2 door(s)
Door opening side	Left (120 °) Right (120 °)
Lock type	4 points lock, handle with 5 mm double bar insert front right door
Mounting plate description	Plain
Type of gland plate	Without gland plate
Accessibility for operation	Rear Sides of enclosure Front
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame: galvanised steel

Uprights: galvanised steel
Door: sheet steel
Panels: sheet steel
Hinge: zamak
Handle: polyamide 6 with 30 % fibre glass

Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net weight	162.023 kg

Environment

Standards	IEC 62208
NEMA degree of protection	NEMA 3R/12
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	164.219 kg
Package 1 Height	213.0 cm
Package 1 width	105.0 cm
Package 1 Length	58.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------