



LOGO! 24RCE, logic module, display power supply / I/O: 24 V AC/DC 24 V/relay, 8 DI/4 DO, memory 800 blocks, modularly expandable, Ethernet, integrated web server, data log, user-defined web pages, standard microSD card for LOGO! Soft Comfort V9.0 or higher older projects executable cloud connection, MQTT in all basic units touch display

Display	
with display	Yes
Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Rated value (AC)	
• 24 V AC	Yes
Line frequency	
• permissible range, lower limit	47 Hz
• permissible range, upper limit	63 Hz
Time of day	
Time switching clocks	
• Number	800; max. 800, function-specific
• Power reserve	480 h
Digital inputs	
Number of digital inputs	8; Of which 4 can be used in analog mode (0 to 10 V)
Digital outputs	
Number of digital outputs	4; Relays
Short-circuit protection	No; external fusing necessary
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes; Radio interference suppression according to EN55011, Limit Value Class B
Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	42.2 kg
— global warming potential, (during production) [CO2 eq]	8.9 kg
— global warming potential, (during operation) [CO2 eq]	33.77 kg

— global warming potential, (after end of life cycle)  
[CO2 eq] -0.43 kg

### Ambient conditions

Ambient temperature during operation	
• min.	-20 °C; No condensation
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)

### Dimensions

Width	71.5 mm; 4 modular widths (MW)
Height	90 mm
Depth	58 mm

### Approvals / Certificates

#### General Product Approval

[Manufacturer Declaration](#)



[Manufacturer Declaration](#)



#### General Product Approval

#### For use in hazardous locations

#### Environment



[CCC-Ex](#)



last modified:

5/9/2026