

# LE1GVMEKA59

Empty enclosures, TeSys LE, with GV2E01 sealing device and neutral terminal, for GV2ME +LC1K



## Main

Range of product	TeSys
Product name	LE
Device short name	LE1GVME
Product or component type	Enclosure
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Contacteur ordered separately Circuit-breaker ordered separately Sealing kit Neutral terminal

## Complementary

Width	101 mm
Height	201 mm
Depth	94 mm
Net weight	0.74 kg
Cable entry number	2 ISO20 top 2 ISO20 bottom 2 ISO25 top 2 ISO25 bottom

## Environment

IP degree of protection	IP55
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins