

Drywall Cutter LXT®

DSD180

18V • 15 mm

Handy tool for neat and easy cutting of plasterboard

An easy-to-use tool for cutting openings in drywall for installing lights or air-conditioning ducts. This is a handy tool for building and renovation projects. Adjustable cutting depth of up to 15 mm. Comes with an efficient dust extraction, especially when connected to a vacuum cleaner.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Impacts per Minute (IPM)	0 - 6000 min ⁻¹
Length of Stroke	6 mm
Max. Cutting Capacity in Wood (90°)	15 mm
Capacity Drywall	30 mm
Blade Diametre	55 x 18 x 0,55 mm
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	1,7 - 2,0 kg
Product Dimensions (L x W x H):	263 x 79 x 291 mm
Orbital Action	✓
Vibration Level, Cutting Boards	5,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,5 m/s ²

User benefits

- Compact and lightweight design
- LED light illuminates the work site
- Depth adjustment
- The base cover and blade cover protect plasterboard surfaces from damage and scratching
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

123559-1

Dust Collector Assembly



456624-4

Base Cover



456632-5

Blade Cover



783201-2

Hex Wrench 3Mm



783202-0

Hex Wrench 4Mm



B-49703

Board Cutter Blade, 2 pcs



B-49719

Board Cutter Blade, 2 pcs



Other

User manual

Parts drawing