



FEIN



CG 7-125

Compact angle grinders, Ø 125 mm

Handy 750 W compact angle grinder for light grinding and cutting.

Product number: 7 225 04 60 00 0

Details

- + Perfect ergonomics thanks to lateral slide switch and small grip dimension.
- + Fatigue-free working thanks to low weight.
- + Solid metal gearbox head can be turned in 90° steps for maximum robustness and service life
- and very good access to difficult-to-reach spots.
- + Enhanced safety through integrated restart protection.

Price includes

- + 1 safety guard
- + 1 pair of flanges
- + 1 key
- + 1 safety hood for cutter
- + 1 additional handle

Product feature

- + Restart protection

Application



Roughing-down



Deburring



Dividing



+ suitable

++ well suitable

Technical data

TECHNICAL DATA

Input

750 W

Output

440 W

Speed, no load

12,000 - rpm

Grinding disc Ø

125 mm

Elast. Backing pad Ø

125 mm

Cable with plug

4 m

Weight according to
EPTA

1.80 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA
Uncertainty of measured value
KpA

95,8 dB
3 dB

Sound power level LWA
Uncertainty of measured value
KWA

103,8 dB
3 dB

Sound peak value

112 dB

LpCpeak
Uncertainty of measured value
KpCpeak

3 dB

Vibration value 1 α_{hv} 3-
way
Uncertainty of measured value
K α

7,2 m/s²
1,5 m/s²

Vibration value 2 α_{hv} 3-
way
Uncertainty of measured value
K α

1,6 m/s²
1,5 m/s²

Application examples



FEIN

