



Part Number : 1069200000
Product Description : Optical Splice Protection Sleeve, Single Fiber, Outer Tube Outer Diameter 2.30mm and Length 40.00mm (After Shrinkage)
Series Number : 106920
Status : Active
Product Category : Optical Fibers



Documents & Resources

Drawings
[1069200000_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Optical Fibers
Series	106920
Description	Optical Splice Protection Sleeve, Single Fiber, Outer Tube Outer Diameter 2.30mm and Length 40.00mm (After Shrinkage)
Application	Fiber Closure Installation, Field Fiber Splicing Assembly, Manufacturing, Network Infrastructure
Product Name	Optical Splice Protection
UPC	196823222108

Physical

Cable Length	40.00mm
Color - Cable Jacket	Clear
Internal Diameter	1.50mm
Material - Outer Jacket	Polyolefin
Outer Diameter	2.30mm
Packaging Type	Bag
Temperature Range - Operating	-55° to +105°C
Wire/Cable Type	N/A