




ECN MARK	ECN NO.	DESCRIPTION	DATE



7P+5C(30AWG)

(1/0.23BC*1P+1/0.23BC+AL+MY)*7P+
1/0.23BC*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG
PVC Jacket



7P+5C(28AWG)

28+30# OD8.6
(1/0.32BC*1P+1/0.23BC+AL+MY)*7P+
1/0.23BC*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG
PVC Jacket

LENGTH	AWG
10000mm	28AWG OD:8.6
7500mm	28AWG OD:8.6
5000mm	30AWG OD:7.3
3000mm	30AWG OD:7.3
2000mm	30AWG OD:7.3
1000mm	30AWG OD:7.3

NO.	QTY.	DESCRIPTION/SPECIFICATIONS	REMARKS	TOLERANCE	SIGNATURES	DATE	CPDVI002								
5	2PC	PVC BLACK					<table border="1"> <tr> <td>SCALE</td> <td>TITLE</td> <td></td> </tr> <tr> <td>REV</td> <td>A1</td> <td>DRG NO</td> </tr> </table>			SCALE	TITLE		REV	A1	DRG NO
SCALE	TITLE														
REV	A1	DRG NO													
4	4PC	Cover			DRAFT: Jay										
3	1PC	DVI Male 24+1PIN Gold plated		20-49 ±0.00 100-999 ±0.00 1000-9999 ±0.00 10000-99999 ±0.00	CHECKED: Neo										
2	1PC	DVI Male 24+1PIN Gold plated			APPROVAL: James										
1	1PC	PVC BLACK													
NO.	DRG NO	DESCRIPTION/SPECIFICATIONS	QTY.	REMARKS	Unit:MM	REV	A1	DRG NO							

