



Cut



Medium Duty

Our best Cut Sleeves, now made green

- **Heightened defenses:** INTERCEPT™ Cut Resistance Technology's blend of synthetic and natural fibers ensures superior protection, especially when combined with HyFlex® cut-resistant gloves
- **Elevated comfort:** HyFlex® 11-280 protective arm sleeves also deliver superb comfort, with a seamless design and HPPE yarn that ensures a cool, breathable feel
- **Food handling compliance:** They adhere to FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600, for safe food handling and compliant workplace safety
- **Varied sizing options:** HyFlex® 11-280 sleeves come in wide and narrow versions, with multiple length options
- **Certified harm-free:** They also benefit from Oeko-Tex® certification, certifying them free of substances harmful to human health
- **Sustainable design:** HyFlex® 11-280 sustainable sleeves are designed with 20% recycled content* reducing our carbon footprint by 47g CO2eq/piece**



*% is the minimum recycled content in final product

** vs standard nylon sleeve

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Food Processing
- Utilities
- Warehousing

Applications

- Glass repair and replacement
- Handling metal sheets & panels

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-280

High cut protection sleeve with excellent breathability

Key Features

- **EN ISO CUT D & ANSI/ISEA 105-2024 CUT A4-rated protection:** Advanced knitwork designed using INTERCEPT[™] Cut Resistance Technology
- **Seamless design and various length options:** Ideal fit, daily comfort
- **HPPE yarn:** For protective sleeves that offer a cool, breathable feel
- **Sleeve made with 20% recycled content*:** Carbon footprint reduction of 47g CO₂eq/piece**

*% is the minimum recycled content in final product

** vs standard nylon sleeve

Technologies



Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	LENGTH	PACKAGE
HyFlex [®] 11-280	Liner Material: Ansell INTERCEPT [™] Technology Cuff Style: Knitwrist without thumbslot	15	12" (30 CM), 16" (40 CM), 18" (45 CM), 22" (55 CM)	50 sleeves/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

