

Datasheet

RS Pro Plain Steel Insert, M4, 9mm

RS Stock No: **425-7531**



Product Details

RS Pro crimp nut insert is suitable for screw fixing to thin panels wherever rear access is impossible. While fitting, the serrated part of the nut expands inside the hole to provide high torque resistance. The special design of this nut ensures excellent resistance to rotation and vibration. The insert features 9 mm flange diameter and has M4 threads.

Features and Benefits

- Crimp nuts for screw fixing to thin panels wherever rear access is impossible
- When fitting, the serrated part of the nut expands inside the hole to provide high torque resistance
- The special design of these nuts ensures excellent resistance to rotation and vibration
- Both flanged and flush type nuts can be fitted with the same tool



Specifications:

Body Depth	11.3 mm
Body Outside Diameter	9 mm
Finish	Plain
Fixing Hole Diameter	6 mm
Flange Diameter	9 mm
Material	Steel
Thickness of Material Maximum	3 mm
Thickness of Material Minimum	0.5 mm
Thread Size	M4