


KEMET Part Number: C20ALGR5330AASK



Capacitor, film, Metallized Polypropylene, 33 uF, +/-10% Tol, -25/+70C, ACFilter, 640 VAC



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	75	+/-0.5
L	147	+/-2
S	35	+/-1

Notes:

-W = 21 +/-1

-W1 = 45 +/-1

General Information

Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	ACFilter
Style:	Aluminum Can
Features:	Single Phase PFC
Mounting Type:	Bolt: M12x16
RoHS:	Yes

Specifications

Capacitance:	33 uF
Voltage:	1400 V
Tolerance:	+/-10%
Voltage AC:	640 VAC
Rated Temperature:	70C
Temperature Range:	-25/+70C
Maximum dVdT:	30 v/us
Insulation Resistance:	10 MOhm
Current/Ripple Current:	40 Amps (10kHz 40C)
Resistance/ESR:	2.2 mOhms (10kHz)
Inductance:	135 nH
Miscellaneous:	Thermal Resistance = 9.1 C/W

Packaging Specifications

Package Kind:	Bulk
---------------	------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2016 IntelliData.net