





LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
BD	35				H	REDRAW ON CAD	1-29-92	KB
					J	OBS -2 PER EC 0020-0394-93	11/17/94	RK
					K	OBS -4 PER EC 0020-0136-95	17 JUL 95	AF



OBSOLETE	PER DETAIL F	NO	208495-4
OBSOLETE	AS SHOWN	YES	208495-2
	AS SHOWN	NO	208495-1
	FRONT FACE CONFIGURATION	PERIPHERAL SEAL	PART NO

- 1 CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
2. RECEPTACLE WILL ACCEPT 3 TYPE XII PIN CONTACTS.
- 3 5.08µm [1.000200] MIN NICKEL OVER 10.16µm [1.000400] MIN COPPER.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13[.005] 3 PLC DEC ± - ANGLES ± - MATERIAL RECEPTACLE: NYLON, BLACK RCPT SHELL: ZINC PERIP SEAL: ELASTOMER, GREY PIN: CARBON STEEL FINISH RCPT SHELL: 3 PIN: NICKEL PLATED	DR 1-29-92 W.G.LENKER	AMP AMP Incorporated Harrisburg, PA 17105-3608	
	CHK 2-11-92 D.STONE		
	APPD 2-12-92 K.BEAVER	NAME	
	APPD 2-12-92 C.ROHDE	RECEPTACLE ASSEMBLY, 22-3, STD SEX, CMC	
PRODUCT SPEC -	APPLICATION SPEC -	SIZE C	CAGE CODE 00779
	WEIGHT -	SCALE 2:1	DRAWING NO 208495
		SHEET 1 OF 1	