



Relays & Contactors > Relay Accessories



Relay Socket Type: **Printed Circuit Board**

Product Mount Type: **Board Mount**

Pole Configuration: **3**

Relay Accessory Type: **Socket**

Features

Product Type Features

Relay Accessory Type	Socket
----------------------	--------

Contact Features

Terminal Style	PC
Relay Socket Type	Printed Circuit Board
Pole Configuration	3

Termination Features

Number of Pins	15
Termination Post & Tail Length	5 mm[.197 in]

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1393154-0 PT380524	 TE Part # 5-1415006-1 PT380220	 TE Part # 3-1415366-1 PT270L12	 TE Part # 5-1419135-8 PT380730
 TE Part # 2-1415357-1 PT270T00	 TE Part # 4-1419111-0 PT270006	 TE Part # 1393162-1 PT28802	 TE Part # 1415002-1 PT270R24
 TE Part # 6-1415541-5 PT370LB2	 TE Part # 6-1419111-3 PT370110	 TE Part # 6-1419111-5 PT370512	 TE Part # 5-1419111-0 PT270615



TE Part # 4-1419111-8
PT270524

TE Part # 8-1415026-1
PT370125

TE Part # 4-1419111-3
PT270048

TE Part # 9-1415001-1
PT270L24

TE Part # 6-1419111-6
PT370524

TE Part # 6-1419111-9
PT370730

TE Part # 8-1415534-0
PT280220

TE Part # 2-1415370-1
PT270M10

Also in the Series | SCHRACK Accessories Miniature Relay PT

Relay Accessories(52)

Customers Also Bought

TE Part #1-2834238-1
3P REC, IP67 R/A T/H CONN,NATURE

TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS

TE Part #1-1609112-1
15CS1=F8271

TE Part #4-1879351-5
RR01 5% 200K AMMO

TE Part #63698-1
RING,M4, DIA 4.39,16-12,TPBR

TE Part #1217332-1
187 FASTON,PCB TAB,TCBR

TE Part #8-1879352-5
RR02 5% 1K0 AMMO

TE Part #5205714-7
37 PLUG SP/MS STD



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393162-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393162-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393162-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Accessories - Miniature Relay PT

English

Product Specifications

Definitions General Purpose Relays

English