



ENGLISH

## Datasheet

# RS PRO HSCo 6mm Jobber Drill Bit, 86mm Plain Shank

RS Stock number [216-583](#)



### Description:

RS, Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

### Product Details:

- HSS Colbalt (5%) Jobber Drills
- For use on alloy steel, hardened steel, stainless steel, cast iron & titanium
- Standard : DIN338 right hand spiral
- Material : HSS Cobalt 5%
- Point Angle : 135° split point
- Surface : amber finish



ENGLISH

**Dimensions:**

RS Stock No.	Manu Part No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
216640	H10600100	1.0	34	12
216634	H10600150	1.5	40	18
216662	H10600200	2.0	49	24
216656	H10600250	2.5	57	30
216498	H10600300	3.0	61	33
216482	H10600330	3.3	65	36
216612	H10600350	3.5	70	39
216606	H10600400	4.0	75	43
216628	H10600420	4.2	75	43
216599	H10600450	4.5	80	47
216583	H10600500	5.0	86	52
216577	H10600550	5.5	93	57
216707	H10600600	6.0	93	57
216476	H10600650	6.5	101	63
216460	H10600680	6.8	109	69
216454	H10600700	7.0	109	69
216448	H10600750	7.5	109	69
216432	H10600800	8.0	117	75
216561	H10600850	8.5	117	75
216555	H10600900	9.0	125	81
216549	H10600950	9.5	125	81
216533	H10601000	10.0	133	87
216527	H10601020	10.2	133	87
216511	H10601050	10.5	133	87
216505	H10601100	11.0	142	94
216684	H10601150	11.5	142	94