

Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Rocker
Number of rocker	1
Colour tint	White (RAL 9003)

Complementary

Device mounting	Flush Surface
Actuator	Rocker
Condition of use	Indoor/outdoor
Material	PP (polypropylene) ABS (acrylonitrile butadiene-styrene)
Marking	Light symbol
IP degree of protection	IP55
IK degree of protection	IK08
Width	70 mm
Height	70 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Depth	14 mm

Environment

Quality labels	NF AENOR EAC CE
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration