

Comfortable gloves offering tactility and protection across numerous applications

- **Elevated comfort:** Ansell MICROFLEX® 92-134 Versatility disposable safety gloves are made of a soft nitrile formulation, which provides a highly comfortable fit and feel while protecting hands
- **Heightened tactility:** These nitrile disposable gloves' lightweight construction provides augmented tactile sensitivity and fine motor control
- **Optimized grip:** These MICROFLEX® gloves are textured on the fingertips to ensure a stronger grip for the safer handling of tools and materials
- **Genuine versatility:** Designed for a broad range of applications, these gloves reinforce hand protection across a wide range of industries



Industries

- Healthcare
- Automotive
- Food Processing
- Janitorial / Sanitation
- Manufacturing
- Life Sciences
- Government

Recommended For

- Standard patient examinations
- Picking parts and accessories
- Food processing and handling
- Catering/Meal preparation
- Disposal of waste (trash, biohazard and linens)
- Light assembly tasks
- Lab work, blending, compounding, filling, cleaning
- Preparing pharmaceutical products
- Laboratory analysis

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, Korean Standard, ASTM D6319, CE 0493, IFU, EN 16523-1, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, EN 455 1-4, EN ISO 21420:2020, FDA21 CFR 177-2600-US Food Contact Approved, US QSR/FDA 510(k) Medical Examination Grade, EU Food Contact Approved, ISO 13485, ISO 18889:2019, ISO 9001, PMDA Notification Number: 13B3X10307AH0001, Trade Name: Ansell Non Latex Medical Examination Glove, UKCA, Anvisa 81496190020 / CA 48.121, INVIMA 2015DM-0013417
Packaging Overview	100 gloves per dispenser, 10 dispensers per case, 1000 gloves per case 90 gloves per dispenser (Size XXL), 900 gloves per case (Size XXL)
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	China
Product Segmentation	Standard Thin
Antistatic	No
Silicone Free	No
Vulcanization Chemical Accelerators	- Zinc Dibutyldithiocarbamate (ZDBC) - Zinc Diethyldithiocarbamate (ZDEC) Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D6319
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D6319
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D6319
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412 & D573
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	92134060	92134070	92134080	92134090	92134100	92134110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY: +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR: +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
---	--	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

