




Part Number : [2262452044](#)
Product Description : Mini-Fit Versa Color-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 600.00mm Length, 4 Circuits, Blue
Series Number : 226245
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2262452044_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	226245
Description	Mini-Fit Versa Color-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 600.00mm Length, 4 Circuits, Blue
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mini-Fit Versa Color-to-Pigtail
Product Name	Mini-Fit Versa Color
Type	Discrete Wire Assembly
UPC	198282202882

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Cable Length	600.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Blue
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	9.189/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag

Pitch - Mating Interface	4.20mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Insulation Diameter	2.45mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Plug Housings	<u>46993</u>
Mini-Fit Vertical Dual Row Headers	<u>172447</u>