

Surface Switches



Options available

- Less Enclosure - add LE to Catalogue Number e.g. 56SW320 becomes 56SW320LE.
- Resistant Orange - add RO to Catalogue Number e.g. 56SW320 becomes 56SW320,RO
- Resistant White - add RW to Catalogue Number e.g. 56SW320 becomes 56SW320,RW
- Chemical Grey - add CG to Catalogue Number e.g. 56SW320 becomes 56SW320,CG.
- 56SW320CX - replaces 56SW320C control switch

56 Series Surface Switches

56 Series Surface Switches are available from 250V, 10A to 500V 63A. They incorporate a positive, rotary switch action. 'ON' and 'OFF' positions are clearly marked and there is provision for two padlocks. Hole diameter is 8mm.

If locking is required in the 'ON' position, simply drill a hole where necessary.

All 63A switches come with the facility to fit auxiliary micro switch 56SWAUX15.

To provide easier wiring of our 56 Series Three Pole 63A Switch, a deeper two gang enclosure and centrally mounted option (Cat. No. 56SW363/2), allows additional room for wiring associated with this application.


Earth and neutral connectors accommodating 3 x 6mm² cables are supplied with all products above 20A.

56SW332LE-GY: 3 Pole, 32A, 500V

I _e (A) Utilisation Category			M Rating
AC21A	AC22A	AC23A	
32	32	28	M180

Conductor Terminal size in mm ²		IP Rating	O/A Dims. (H) x (W) x (D)
Min.	Max/Cond.		
4	16	66	107x101x108

Switching Wire Diagram



Switch terminals are not identified
 Switch is backwired
 Conductor termination is plain screw type

56SWH	66CV450	56SW363/2	56C610	56C432	56C550
56SWH 325	66CV463	56SW363	56C710	56C532	56CV540
56SWH 363		56SW350	56C720	56C450	56CV550
56SWH 340		56SW332	56C440	56C540	56SW310
56SWH 380					56SW320