

Datasheet

LUMINAIRE SPECIFICATIONS

ILLUSTRATION



DESCRIPTION		
DETAILS	Manufacturer	Orbik Electronics Limited
	Model Catalogue No	NA8/NM3/E
	Country of Origin	United Kingdom
	CE Mark Compliance	CE marked REACH and RoHS compliant
	Compliance to Standards	EN60598.2.22: 1999
	Manufacturing Quality Approval	ISO9001: 2008
CONSTRUCTION	Luminaire Dimensions	350mm x 108mm
	Housing construction	850° C polycarbonate
	Body finish	White
	Protection Degree	IP65
	Insulation class and supply voltage	Class 1 230/240 50/60Hz
GEAR	Control gear manufacturer / type	Orbik P996 inverter/charger
	Power factor correction	>0.85
	Radio interference compliance	EN55015
	Harmonics compliance	EN61000-3-2 Class C
	Batteries employed	3 x 1.5 Ah high temp Ni-CAD
DIFFUSER	Light distribution category	Exit signage
	Luminaire BLF output	Not Applicable for signage
	Reflector material	-
	Reflector type	-
	Reflector finish	-
	Legend material	Self-extinguishing plastic
	Legend type	Integral
	Legend finish	Euro Legend style
LAMP	Lamp Wattage and Type	Hybec or approved equivalent T5 8W fluorescent
	Lamp Manufacturer	Hybec (16713)
	Average rated life	5000
	Initial lumen output	400
	CCT (°C)	4000