

FR406 - PW3 FR Modaflame Hi-Vis Work Trousers

Collection: PW3

Shell Fabric: Modaflame Work HV: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre

Outer Carton: 18

Product information

Constructed using Inherent Modaflame, this contemporary FR Hi-Vis Work Trousers provides ultimate wearer comfort. FR durable reinforcement fabric at key abrasion points and triple stitching throughout guarantees maximum durability. This trousers features top loading kneepad pockets and an easy access multiway thigh pocket for secure storage of your phone, keys and tools.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.



Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 6.4 CAL/CM², EBT 6.8 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 13034 Type PB [6]

EN ISO 20471 Class 2

Features

- Inherent flame resistant qualities will not diminish with washing
- Reinforced panels in high wear areas for maximum durability
- Twin-stitched seams for extra durability
- UKCA marked
- CE certified
- Heat applied segmented reflective tape for added visibility
- 40+ UPF rated fabric to block 98% of UV rays
- 8 pockets for ample storage
- Adjustable hem to accommodate all leg lengths
- Side elastic waist for ultimate wearer comfort
- Top-loading knee pad pockets for quick and easy access

FR406 - PW3 FR Modaflame Hi-Vis Work Trousers

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR406YBR28	Yellow/Black	60.0	40.0	36.0	0.8780	0.0864	5036108396023	25036108880885
FR406YBR30	Yellow/Black	60.0	40.0	36.0	0.9000	0.0864	5036108396030	25036108880892
FR406YBR32	Yellow/Black	60.0	40.0	36.0	0.9160	0.0864	5036108396047	25036108880908
FR406YBR33	Yellow/Black	60.0	40.0	36.0	0.9280	0.0864	5036108396054	25036108880915
FR406YBR34	Yellow/Black	60.0	40.0	36.0	0.9300	0.0864	5036108396061	25036108880922
FR406YBR36	Yellow/Black	60.0	40.0	36.0	0.9570	0.0864	5036108396078	25036108880939
FR406YBR38	Yellow/Black	60.0	40.0	36.0	0.9760	0.0864	5036108396085	25036108880946
FR406YBR40	Yellow/Black	60.0	40.0	36.0	0.9820	0.0864	5036108396092	25036108880953
FR406YBR41	Yellow/Black	60.0	40.0	36.0	0.9960	0.0864	5036108396108	25036108880960
FR406YBR42	Yellow/Black	60.0	40.0	36.0	1.0110	0.0864	5036108396115	25036108880977
FR406YBR44	Yellow/Black	60.0	40.0	36.0	1.0230	0.0864	5036108396122	25036108880984
FR406YBR46	Yellow/Black	60.0	40.0	36.0	1.0450	0.0864	5036108396139	25036108880991
FR406YBR48	Yellow/Black	60.0	40.0	36.0	1.0520	0.0864	5036108396146	25036108881004