

## Features

- Innovative design with soft lines
- Cases stack inside each other for easier and more efficient storage and freight
- Secure clips
- Die-cut foam

## RS PRO Packaging Case, Polypropylene, w/Foam

RS Stock No.: 0707837,0707838,707838P



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Packaging Case

For ultimate safe and secure transport, the RS PRO transit case provides you with the ideal professional solution. Die-cut foam inserts safely protect any components, sensitive equipment, and documents.

## General Specifications

<b>Material</b>	Polypropylene
<b>Internal Length</b>	See details below
<b>Internal Width</b>	See details below
<b>Internal Height</b>	See details below
<b>Internal Dimensions</b>	See details below
<b>External Dimensions</b>	See details below
<b>Foam</b>	Yes
<b>Watertight or Waterproof</b>	No
<b>Wheels</b>	No
<b>Material Type</b>	Plastic
<b>Colour</b>	Black
<b>Dividers</b>	No
<b>Weight</b>	See details below

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Weight (Kg)
XXX-XXXX 0707837,0707838,707838P	RS PRO	Transit Case	385 x 235 x 98	395 x 300 x 103	0.60
XXX-XXXX 0707839,0707840,707840P	RS PRO	Transit Case	248 x 160 x 39	260 x 210 x 44	0.267
XXX-XXXX 0707841,0707842,707842P	RS PRO	Transit Case	363 x 244 x 115	370 x 307 x 121	0.645
XXX-XXXX 0707843,0707844,707844P	RS PRO	Transit Case	272 x 190 x 73	280 x 240 x 76	0.29

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Colour	IP Rating
XXX-XXXX 0707755,0707756,707756P	RS PRO	Waterproof Case	235 x 180 x 105	258 x 243 x 117.5	Black	IP67
XXX-XXXX 0707757,0707758,707758P	RS PRO	Waterproof Case	235 x 180 x 156	258 x 243 x 167.5	Black	IP67
XXX-XXXX 0707761,0707762,707762P	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	Black	IP67
XXX-XXXX 0707763,0707764,707764P	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	Black	IP67
XXX-XXXX 0707765,0707766,707766P	RS PRO	Waterproof Case	212 x 140x 47	230 x 175 x 53	Black	IP67
XXX-XXXX 0707768,0707769,707769P	RS PRO	Waterproof Case	316 x 195 x 53	350 x 230 x 59	Black	IP67
XXX-XXXX 0707770,0707771,707771P	RS PRO	Waterproof Case	316 x 195 x 81	350 x 230 x 86	Black	IP67
XXX-XXXX 0707759,0707760,707760P	RS PRO	Waterproof Case	426 x 290 x 159	464 X 366 X 176	Black	IP67
XXX-XXXX 0707772,0707774,707774P	RS PRO	Watertight Case	380 x 270 x 115	414 x 345 x 129	Black	IP67
XXX-XXXX 0707775	RS PRO	Watertight Case	465 x 335 x 125	502x 415 x 141	Black	IP67
XXX-XXXX 0707776,0707777,707777P	RS PRO	Watertight Case	380 x 270 x 160	414 x 345 x 174	Black	IP67
XXX-XXXX 0707778,0707779,707779P	RS PRO	Watertight Case	400 x 230 x 260	456 x 290 x 318	Black	IP67
XXX-XXXX 0707780	RS PRO	Watertight Case	465 x 335 x 220	502 x 415 x 246	Black	IP67
XXX-XXXX 0707781	RS PRO	Watertight Case	500 x 350 x 280	555 x 428 x 306	Black	IP67
XXX-XXXX 0707782	RS PRO	Watertight Case	800 x 370 x 140	850 x 440 x 158	Black	IP67
XXX-XXXX 0707783	RS PRO	Watertight Case	750 x 480 x 400	816 x 540 x 426	Black	IP67
XXX-XXXX 0707784,0707785,707785P	RS PRO	Watertight Case	212 x 140 x 47	230 x 175 x 53	Black	IP67
XXX-XXXX 0707786,0707787,707787P	RS PRO	Watertight Case	258 x 243 x 118	366 x 464 x 176	Orange	IP67
XXX-XXXX 0707788,0707790,707790P	RS PRO	Watertight Case	258 x 243 x 168	366 x 464 x 176	Orange	IP67
XXX-XXXX 0707791,0707792,707792P	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	Orange	IP67
XXX-XXXX 0707793,0707794,707794P	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	Brown	IP67
XXX-XXXX 0707796,0707797,707797P	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	Orange	IP67
XXX-XXXX 0707798,0707799,707799P	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	Brown	IP67
XXX-XXXX 0707800	RS PRO	Watertight Case	500 x 350 x 211	555 x 428 x 211	Orange	IP67
XXX-XXXX 0707803	RS PRO	Roller Watertight Case	500 x 350 x 280	555 x 428 x 326	Black	IP67

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Colour	IP Rating
XXX-XXXX 0707804	RS PRO	Roller Watertight Case	620 x 460 x 250	687 x 528 x 276	Black	IP67
XXX-XXXX 0707805	RS PRO	Roller Watertight Case	620 x 460 x 340	687 x 528 x 376	Black	IP67
XXX-XXXX 0707801	RS PRO	Roller Watertight Case	538 x 405 x 245	604 x 473 x 283	Black	IP67
XXX-XXXX 0707823,0707825,707825P	RS PRO	Packaging Case	415 x 280 x 125	465 x 355 x 145	Black	IP65
XXX-XXXX 0707826,0707827,707827P	RS PRO	Packaging Case	415 x 280 x 190	465 x 355 x 210	Black	IP65
XXX-XXXX 0707828,0707829,707829P	RS PRO	Packaging Case	520 x 350 x 125	572 x 425 x 144	Black	IP65
XXX-XXXX 0707837,0707838,707838P	RS PRO	Packaging Case	385 x 235 x 98	395 x 300 x 103	Black	N/A
XXX-XXXX 0707839,0707840,707840P	RS PRO	Packaging Case	248 x 160 x 39	260 x 210 x 44	Black	N/A
XXX-XXXX 0707841,0707842,707842P	RS PRO	Packaging Case	363 x 244 x 115	370 x 307 x 121	Black	N/A
XXX-XXXX 0707843,0707844,707844P	RS PRO	Packaging Case	272 x 190 x 73	280 x 240 x 76	Black	N/A
XXX-XXXX 0707831,0707832,707832P	RS PRO	Transit Case	324 x 252 x 87	340 x 298 x 96	Black	N/A
XXX-XXXX 0707833,0707834,707834P	RS PRO	Tool Case	N/A	420 x 303 x 400	Blue/White	N/A
XXX-XXXX 0707835,0707836,707836P	RS PRO	Tool Case	N/A	420 x 303 x 400	Blue/White	N/A
XXX-XXXX 0707806,0707807,707807P	RS PRO	Assortment Box	157 x 82 x 41	175 x 115 x 47	Transparent	IP67
XXX-XXXX 0707808,0707809,707809P	RS PRO	Assortment Box	212 x 140 x 47	230 x 175 x 53	Transparent	IP67
XXX-XXXX 0707810,0707811,707811P	RS PRO	Assortment Box	316 x 230 x 53	350x 230 x 59	Transparent	IP67
XXX-XXXX 0707821,0707822,707822P	RS PRO	Assortment Box	315 x 240 x 46	325 x 255 x 56	Transparent	N/A
XXX-XXXX 0707812,0707813,707813P	RS PRO	Assortment Box, 6 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
XXX-XXXX 0707814,0707815,707815P	RS PRO	Assortment Box, 10 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
XXX-XXXX 0707816,0707817,707817P	RS PRO	Assortment Box, 13 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
XXX-XXXX 0707819,0707820,707820P	RS PRO	Assortment Box, 15 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A

Stock No. xxx-xxx  
170/38N+GPB



- External dimension 395 x 300 x 103H mm
- Internal dimension 385 x 235 x 98H mm
- Weight: 0.62kg



- Innovative design with soft lines
- Cases stack inside each other for easier and more efficient storage and freight
- Secure clips
- Die-cut foam

Stock No. xxx-xxx  
170/26H44+GPB



- External dimension 260 x 210 x 44H mm
- Internal dimension 248 x 160 x 39H mm
- Weight: 0.267kg



- Innovative design with soft lines
- Cases stack inside each other for easier and more efficient storage and freight
- Secure clips
- Die-cut foam

Stock No. xxx-xxx  
170/37+GPB



- External dimension 370 x 307 x 121H mm
- Internal dimension 363 x 244 x 115H mm
- Weight: 0.645kg



- Innovative design with soft lines
- Cases stack inside each other for easier and more efficient storage and freight
- Secure clips
- Die-cut foam

Stock No. xxx-xxx  
170/28



- External dimension 280 x 240 x 76H mm
- Internal dimension 272 x 190 x 173H mm
- Weight: 0.29kg



- Innovative design with soft lines
- Cases stack inside each other for easier and more efficient storage and freight
- Secure clips
- Die-cut foam