

EX01 6H/6G

- spectrum Machine Tap
- spectrum Maschinen-Gewindebohrer
- spectrum Machinetappen
- spectrum Tarauds machine
- spectrum Machos de máquina
- spectrum Macho Máquina



NEW

2010.02



EX01 6H



- 1.1 1.2 1.3 1.4 1.5 2.1 2.2
- 2.3

M	P mm	l ₁ mm	l ₂ mm	d ₂ Ø mm	a mm	l ₃ mm	z	↔	l ₄ mm	e-Code
2	0.40	45	4	2.8	2.1	5	3	1.6	9	EX01M2 ¹⁾
2.5	0.45	50	4	2.8	2.1	5	3	2.05	12.5	EX01M2.5 ¹⁾
3	0.50	56	6	3.5	2.7	6	3	2.5	18	EX01M3
3.5	0.60	56	7	4.0	3.0	6	3	2.9	20	EX01M3.5
4	0.70	63	7	4.5	3.4	6	3	3.3	21	EX01M4
5	0.80	70	8	6.0	4.9	8	3	4.2	25	EX01M5
6	1.00	80	10	6.0	4.9	8	3	5	31	EX01M6
6	1.00	80	10	4.5	3.4	6	3	5		EX01M6DIN376
7	1.00	80	10	7.0	5.5	8	3	6	31	EX01M7
8	1.25	90	12	8.0	6.2	9	3	6.8	35	EX01M8
8	1.25	90	13	6.0	4.9	8	3	6.8		EX01M8DIN376
10	1.50	100	15	10.0	8.0	11	3	8.5	39	EX01M10
10	1.50	100	15	7.0	5.5	8	3	8.5		EX01M10DIN376
12	1.75	110	16	9.0	7.0	10	3	10.3		EX01M12
14	2.00	110	20	11.0	9.0	12	3	12		EX01M14
16	2.00	110	20	12.0	9.0	12	4	14		EX01M16
18	2.50	125	25	14.0	11.0	14	4	15.5		EX01M18 ¹⁾
20	2.50	140	25	16.0	12.0	15	4	17.5		EX01M20 ¹⁾
22	2.50	140	25	18.0	14.5	17	4	19.5		EX01M22 ¹⁾
24	3.00	160	30	18.0	14.5	17	4	21		EX01M24 ¹⁾
27	3.00	160	30	20.0	16.0	19	4	24		EX01M27 ¹⁾
30	3.50	180	36	22.0	18.0	21	4	26.5		EX01M30 ¹⁾
33	3.50	180	36	25.0	20.0	23	4	29.5		EX01M33 ¹⁾
36	4.00	200	40	28.0	22.0	25	4	32		EX01M36 ¹⁾
39	4.00	200	40	32.0	24.0	27	4	35		EX01M39 ¹⁾
42	4.50	200	45	32.0	24.0	27	4	37.5		EX01M42 ¹⁾
48	5.00	250	50	36.0	29.0	32	4	43		EX01M48 ¹⁾
52	5.00	250	50	40.0	32.0	35	5	47		EX01M52 ¹⁾
56	5.50	250	55	40.0	32.0	35	5	50.5		EX01M56 ¹⁾
64	6.00	315	60	50.0	39.0	42	6	58		EX01M64 ¹⁾

EX01 6G



- 1.1 1.2 1.3 1.4 1.5 2.1 2.2
- 2.3

M	P mm	l ₁ mm	l ₂ mm	d ₂ Ø mm	a mm	l ₃ mm	z	↔	l ₄ mm	e-Code
3	0.50	56	6	3.5	2.7	6	3	2.5	18	EX01M36G
4	0.70	63	7	4.5	3.4	6	3	3.3	21	EX01M46G
5	0.80	70	8	6.0	4.9	8	3	4.2	25	EX01M56G
6	1.00	80	10	6.0	4.9	8	3	5	31	EX01M66G
8	1.25	90	12	8.0	6.2	9	3	6.8	35	EX01M86G
10	1.50	100	15	10.0	8.0	11	3	8.5	39	EX01M106G
12	1.75	110	16	9.0	7.0	10	3	10.3		EX01M126G
14	2.00	110	20	11.0	9.0	12	3	12		EX01M146G
16	2.00	110	20	12.0	9.0	12	4	14		EX01M166G
20	2.50	140	25	16.0	12.0	15	4	17.5		EX01M206G ¹⁾

¹⁾ HSCo