


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER	
ORIGINAL	1

NOTES:

CURRENT RATING:	2A AC/DC
VOLTAGE RATING:	100V AC/DC
TEMPERATURE RATING:	-40°C ~ 105°C
CONTACT RESISTANCE:	10mΩ MAX.
HOUSING RESISTANCE:	1000MΩ min.
WITHSTANDING VOLTAGE:	800V AC / 60s
HOUSING MATERIAL:	PA9T, UL94V-0
SOLDER TEMPERATURE	
RESISTANCE:	260°C for 30s MAX







PCB LAYOUT



1.60

2.40

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

- 1.00

2.00