

Features

- UV resistant.
- Highly flexible – ease of handling.
- Abrasion and kink resistance.
- Ultra smooth liner ensuring water flow performance.
- Resistant to repeated pulling, bending, crushing.
- RoHS 3 compliant.
- Maximum operating temperature of +60°C
- Minimum operating temperature of -15°C
- High strength Phthalate free PVC
- Polyester fiber reinforcement
- UV resistant PVC cover

RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336837



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

An outstanding all-terrain UV resistant irrigation hose that delivers exceptional durability, flexibility, and water flow performance.

Manufactured in the UK, kink resistant water hose is the ideal heavy-duty choice for all irrigation purposes, as well as for water supply and delivery applications.

The multi-layered construction using custom formulated materials and our exclusive high tensile braiding reinforcement technology, delivers superior flexibility and resilience in all weather conditions, ensuring performance levels that exceed those of comparable products in the professional hose market.

Applications:

- Horticulture
- Fruit, vegetable growers
- Golf clubs
- Agriculture
- Landscaping
- Industrial
- Construction
- Public sector

General Specifications

Hose Pipe / Flexible Tube	Hose Pipe
Colour	Yellow
Features	Reinforced
Series	RS PRO AQF
Inner Diameter	12.5mm
Outer Diameter	17.5mm
Material	PVC
Hose Pipe Action	Transfer
Maximum Working Pressure	16bar
Suitable Application	Irrigation
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Length	100m
Reinforced	Yes
Bend Radius	100mm
Standards Met	BS 3746