



ENGLISH

Datasheet

**Stock No. 161-7269**

**RS PRO Vertical PDU 16 BS Socket Left hand 3 m BS Plug**



BS1363 13 A plug



## **SPECIFICATIONS:**

**Product Name:** Designated Power Distribution Unit for Cabinet

**Socket Type:** BS1363 135 degree

**Socket Quantity:** 16

**Power Input:** Left end single input

**Bracket Install:** Inverse installation

**Cable with plug:** BS1363 13 A plug

**Control Function:** No controlling function

**Protection Function:** 2017 hot swaps module

**Case:** Black

**Cable Specification:** 3 x 1.5 mm<sup>2</sup> x 3 M

**Product Size:** L x W x H = 1374 x 44.4 x 62 mm

**Mounting Length:** 1348 mm

**Case Length:** 1318 mm

**Fittings:** 2 pcs  $\phi 6 \times 16$  mm cross bolt, 2 pcs M6 float nut, PDU manual, 1 pc 155 mm cover plate

## **Electrical Characteristics:**

**Rating voltage:** 250 V ac 50/60 Hz

**Rating Current:** 13 A

**Max. Power:** 3250 W

**Safety Authentication:** CE

**Operating Temperature:** 0 - 50°C, relative humidity 0 - 95%

## **Applications:**

PDU - Power Distribution Unit is widely used in network enclosure and server rack of data center in field of information technology, telecom, electric, power, finance and insurance, aviation, transportation, hospital, education, E-government etc.