

FEATURES

- Straight tip combination pliers
- Made from steel
- Overall length of 160 mm
- Hard wire cutting capacity of 1.6 mm
- Screw cutting capacity of M3.5
- Safety note: The insulating properties of these pliers are not guaranteed and they should NOT be used on or near energized systems

RS PRO Steel Pliers Combination Pliers, 160 mm Overall Length

RS Stock No.: 541-7087



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These combination pliers do double duty as flat-nose pliers with a built-in cutter. Suitable for professionals and DIY use, they can be used to grip, twist or bend wire and cable. Bow handles provide maximum leverage and comfort, while an ergonomic design means you can work for longer without suffering hand fatigue. The pliers are 160 mm long and made of steel to provide superior performance and extended working life. The gripping zone can grasp both flat and round materials. The cutting edge can cut steel wire up to 1.6 mm thick.

General Specifications

Plier Type	Combination Pliers
Non Sparking	Yes
Tip Style	Straight
Material	Steel
Application	Gripping, twisting or bending of wire and cable

Mechanical Specifications

Cutting Capacity	1.6mm
Material Cutting Capability	Hard Wire
Overall Length	160mm

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------

