

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

These Aurora DIMMABLE LED Bulbs are unique in the market whereas they are able to be situated in a fire rated can without loss of lifetime. They have a revolutionary heat sync inside the bulb which pulls heat away from the heat sensitive components leading to longer life in areas where heat build up can be an issue. They will replace a standard GU10 50W halogen bulb happily and we guarantee them for 3 Years.

Product Image:



Product Features:

- High output LED lamp
- CrystalCool™ next generation thermal management offers brighter light for longer
- Engineered for use in suitably ventilated luminaires
- Smooth and linear dimming on most dimmers (dimable versions)
- ErP compliant - High colour rendering index (Ra) >80
- (L70) at a 25,000 hour lifetime
- 3 Year Warranty - see www.auroralighting.com for details

Product Specs:

Input Voltage	220~240V AC
Dimmable	No
Dimensions	58mm (OL) x 58mm

Compliance & Approvals:



SKU Table and Ordering

Warranty:

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Sales

16 Alban Park Hatfield Road
St. Albans AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Distribution

Apex Park 6 Little Burrow
Welwyn Garden City AL7
4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21