



#### **Slide calliper with instant adjustment**

Measurement range: 150 mm  
Reading: 0.05 mm + 1 / 128 in.  
Jaw length: 40 mm  
Hardened stainless steel  
Matt-chrome vernier and scale

#### **Vernier Calipers**

##### **Stainless Steel versions:**

Precision calipers for accuracy in a wide range of measuring applications. Fully hardened stainless steel construction with an anti-glare, satin chrome finish. All measuring surfaces are ground and lapped for high accuracy.

##### **General Information:**

There are four basic measuring methods: inside, outside, depth and step.