



## 1/2" IMPACT WRENCH - TORQUE CONTROL - 90-130 NM

**RC2780T**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:39





## DESCRIPTION

### 1/2" IMPACT WRENCH - TORQUE CONTROL - 90-130 NM

Lightweight housing (composite/aluminium) and ergonomic handle make working with the RC2780T easy.

Limited torque selectable at 90 or 130 NM.

Double hammer mechanism reduces vibration, increases service life and delivers higher torque. Heavy-duty design. Equipped with a switch for reversing the tightening/untightening direction.

## STANDARDS / DIRECTIVES

2006/42/CE

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:39



**SPECIFIC DATA**

Designation	1/2" IMPACT WRENCH TORQUE LIMITED
Sales reference	RC2780T
L (mm)	193
Weight (g)	2000
Rotation speed (rpm)	6 500
Vibration (m/s <sup>2</sup> )	5,4
Noise level (dBa)	85
C mm	6,3
C min mm	1/4"
C mm	90 - 130
Maximum input torque Nm	
Hammer type	M2   SAM Equipment and Machine Guarantee
Guarantee	

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

>> [Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

