



Leiterquerschnitt / wire gauge: 1,5mm<sup>2</sup> / AWG 16  
 Abisolierlänge / stripping length: 9mm

All Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ Free size tolerances	
			Dat.	Name	Massstab/ Scale <b>5:1</b>	Han C Buchsenkontakt, gedreht 40A Han C female contact, turned 40A versilbert / silver plated
			Detail.	05.03.10 Pe		
			Insp.	Tie		
			Stand.			
A			HARTING Electric GmbH & Co. KG			TB 09 32 000 6204 Sub. TB 09 32 000 6204. v. 20.12.05
Mod.	Dat.	Name	D-32339 Espelkamp			
						Blatt/ page