



Features

• SylWork offers a range of high-performance LED work lights, available in both mains-powered and battery-operated models. Designed for ultimate flexibility, SylWork provides reliable, temporary lighting for a variety of DIY projects, including home decorating, household repairs, cleaning, tidying, and general maintenance tasks. The SylWork Inspection Mini is a portable, battery-operated inspection light, perfect for worksite tasks, camping, and outdoor activities. Its compact design makes it easy to carry, while the built-in hook allows for convenient hands-free use. The light is easily rechargeable with the included USB cable and features three-step dimming along with a flashing mode for emergency situations. Lightweight yet durable, it provides a practical lighting solution for various needs and comes with a three-year warranty. Ideal for both professional and home use.

Product Overview

Product name	SylWork Inspection Mini
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
ETIM Class	EC000347
Fixture luminous flux (lm)	480
Correlated colour temperature (k)	6500
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	120
Photobiological Risk Group	RG1
Total power consumption (W)	7.5

## SylWork Inspection Mini 0090202

Electrical protection	Class III
Control gear type	Not required
Dimmable	No
Housing colour	Black
IP rating	IP54
IK rating	IK06
Product EAN number	5410288902029
Warranty	3 years
Dimming method	N/A

### Data table

#### GENERAL DATA

Product name	SylWork Inspection Mini
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
Operating temperature range (°C)	-10°C...+40°C
ETIM Class	EC000347
Warranty	3 years

#### OPTICAL DATA

Fixture luminous flux (lm)	480
Correlated colour temperature (k)	6500
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	120
Distribution type	None
Photobiological Risk Group	RG1

#### ELECTRICAL DATA

## SylWork Inspection Mini 0090202

Total power consumption (W)	7.5
Electrical protection	Class III
Control gear required	No
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	DC

### PHYSICAL DATA

Housing colour	Black
IP rating	IP54
IK rating	IK06
Diffuser finish	Prismatic, Transparent
Diffuser material	PC Polycarbonate
Reflector finish	Not Applicable
Nominal Product Length (mm)	337.5
Nominal Product Width (mm)	30
Nominal Product Height (mm)	30
Weight (kg)	0.192

### PACKAGING

Product EAN number	5410288902029
Packaging single length / height (cm)	34.5
Packaging single width (cm)	4.0
Packaging single depth (cm)	3.5
DUN14 (inner)	15410288902026
Units per outer package	40
Packaging outer length / height (cm)	39.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	38.5

### SAFETY DATA



SylWork Inspection Mini  
0090202

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-10-40
Special purpose lamp	No
Dry applications use only	No
Suitable for household illumination	No